

# Hoistway/Hatch Switches

UL LISTED, CSA CERTIFIED

## EECO LS-1B limit switch



Part Number	Description
LS-1B	Limit switch, for setting zoning, normal and final limits, 1 NO and 1 NC contacts, rated for 300VAC@8A or 230VDC@1A



## EECO MV-4C magnet switch



Part Number	Description
MV-4C	Permanent magnet switch, for zone switches and leveling control units, dead zone, < 1/8 in. @ 1/4 in. gap, 1 NO and 1 NC contacts, rated for 300VAC@8A or 230VDC@1A



## EECO LS-1W limit switch



Part Number	Description
LS-1W	Limit switch, like LS-1B above but with weatherproof design

## EECO MV-4W magnet switch



Part Number	Description
MV-4W	Permanent magnet switch, like MV-4C above but with weatherproof design

## EECO LS-1D limit switch



Part Number	Description
LS-1D	Limit switch, for setting zoning, normal and final limits, 2 NO and 2 NC contacts, rated for 300VAC@8A or 230VDC@1A



## EECO MV-4D magnet switch



Part Number	Description
MV-4D	Permanent magnet switch, for zone switches and leveling control units, dead zone < 1/8 in. @ 1/4 in. gap, 2 NO and 2 NC contacts, rated for 300VAC@8A or 230VDC@1A



## EECO LS-1DW limit switch



Part Number	Description
LS-1DW	Limit switch, like LS-1D above but with weatherproof design

## EECO MV-4DW magnet switch



Part Number	Description
MV-4DW	Permanent magnet switch, like MV-4D above but with weatherproof design

## Mounting bracket for EECO switches

Part Number	Description
LS-1B-BRKT	Mounting bracket, for all EECO limit/magnetic switches

## Magnet inductor switch



Part Number	Description
LDS3004A	Permanent magnet inductor switch, for slowdown and landing positions, recommended for retrofit of EECO vane-operated landing systems, 1 NO and 1 NC contacts, rated for 250VDC@0.5A

