

## Sirocco Equipment Spares & Accessories

Prysmian Part Number: See Individual Descriptions

### 2 & 4 Fibre Guide

Part No. XBFSC00056

Plumettaz Part No. N273.120

Used in the Sirocco Blowing Head when installing either 2 or 4 fibre units.

Usage – 1 per Blowing Head. Pack of 1.




### 8 & 12 Fibre Guide

Part No. XBFSC00057

Plumettaz Part No. N273.057

Used in the Sirocco Blowing Head when installing either 8 or 12 fibre units. This must be used in conjunction with XBFSC00050.

Usage – 1 per Blowing Head. Pack of 1.



### 8 & 12 Fibre Seal

Part No. XBFSC00050

Plumettaz Part No. N273.132

Used in the Sirocco Blowing Head when installing either 8 or 12 fibre units. This must be used in conjunction with XBFSC00057.

Usage – 1 per Blowing Head. Pack of 6



### 6 Fibre Brass Guide

Part No. XBFSC00323

Plumettaz Part No. N273.172

Used in the Sirocco Blowing Head when installing a 6 fibre unit.

Usage – 1 per Blowing Head. Pack of 1.



### 8 Fibre Brass Guide

Part No. XBFSC00174

Plumettaz Part No. N273.147

Used in the Sirocco Blowing Head when installing an 8 fibre unit. The wear characteristics of this guide are superior to that of XBFSC00057 & XBFSC00050.

Usage – 1 per Blowing Head. Pack of 1.



### 5mm Duct Insert

Part No. XBFSC00058  
Plumettaz Part No. N273.108

Used in the Sirocco Blowing Head when installing a fibre unit into a 5/3.5mm tube.

Usage – 1 per Blowing Head. Pack of 1.



### 5mm Duct 'O' Ring

Part No. XBFSC00097  
Plumettaz Part No. N273.066

Used in the Sirocco Blowing Head when installing a fibre unit into a 5/3.5mm tube. This must be used in conjunction with XBFSC00058.

Usage – 1 per Blowing Head. Pack of 6.



### Drive Wheel Tyre

Part No. XBFSC00059  
Plumettaz Part No. N273.230

Used in the Sirocco Blowing Head to drive the fibre unit into the tube.

Usage – 1 per Blowing Head. Pack of 1.



### Idle Wheel

Part No. XBFSC00060  
Plumettaz Part No. N273.123

Used in the Sirocco Blowing Head to drive the fibre unit into the tube. This wheel contains the magnets that operates the length counter.

Usage – 1 per Blowing Head. Pack of 1.



### Blowing Head Control Unit

Part No. XBFSC00109  
Plumettaz Part No. N406.057

This controls the speed and direction of the drive wheel within the blowing head.

Usage – 1 per Blowing Head. Pack of 1.



### Speed & Length Counter

Part No. XBFSC00235  
Plumettaz Part No. N403.001

This indicator displays distance, speed and cumulative distance. This unit can only be fitted to a blowing head that has had one fitted previously.

Usage – 1 per Blowing Head. Pack of 1.



## Blowing Head Air Connector Adapter

Part No. XBFSC00051

This enables the Blowing Head to be connected directly to the compressor. It is used when working in a confined space.

Usage – 1 per Blowing Head. Pack of 1.



## Air Stone

Part No. XBFSC00052

This is connected to the remote end of the installation route and is designed to collect any debris that may be blown through the tube.

Usage – 1 per Blowing Head. Pack of 1.



## Pressure Indicator to 5mm Tube Connector

Part No. XBFSC00053

When recovering an installed fibre unit this is used to connect the Pressure Indicator to the 5mm tube.

Usage – 1 per Blowing Head. Pack of 1.



## Air Hose to 5mm Tube Connector

Part No. XBFSC00054

When recovering an installed fibre unit this is used to connect either the compressor Air Hose or the Compressor to the 5mm tube.

Usage – 1 per Blowing Head. Pack of 1.



## Airflow Gauge

Part No. XBFSC00278

This gauge is used to measure the airflow through a BF tube.

Usage – 1 per Blowing Head. Pack of 1.



## 24v dc Power Plug

Part No. XBFSC00283

Used to connect the blowing head control unit to the power socket on the compressor.

Usage – 1 per Blowing Head. Pack of 1.



## Compressor Air Filter Spares.

Description	Replacement Interval	Norgren Part No.	Prysmian Part No.
Pre-filter	Annual	FIL0245	
Pre-filter Service Kit		5925-02	
Coalescing Filter	6 Months	FIL0246	
Coalescing Filter Service Kit		5925-09	
Carbon Filter	6 Months	FIL0247	
Carbon Filter Service Kit		4241-01	
Pressure Maintaining Valve		VAL0131	
On/Off 3 Way Valve		VAL0181	

Nominal Dimensions & Weights

Item Description	Item Code	Length (mm)	Max. Dia (mm)	Weight (gms)
2 & 4 Fibre Guide	XBFSC00056	74.0	29.0	155.0
8 & 12 Fibre Guide	XBFSC00057	74.0	29.0	130.0
8 & 12 Fibre Seal	IXBFSC00050	7.5 (dia) x 3.5 (h)		0.13
6 Fibre Brass Guide	XBFSC00323	74.0	29.0	151.0
8 Fibre Brass Guide	XBFSC00174	74.0	29.0	151.0
5mm Duct Insert	XBFSC00058	75.0	29.0	127.0
5mm Duct 'O' Ring	XBFSC00097	11.0 (dia) x 3.0 (h)		0.25
Drive Wheel	XBFSC00059	102 (dia) x 12.3 (h)		32.0
Idle Wheel	XBFSC00060	50.0 (dia) x 13.0 (h)		52.0
Blowing Head Control Unit	XBFSC00109	130 x 130 x 108		450.0
Blowing Head Air Connector Adaptor	XBFSC00051	87.0	23.0	130.0
Air Stone	XBFSC00052	77.0	25.0	39.0
Pressure Indicator To 5mm Tube Connector	XBFSC00053	59.0	21.0	57.0
Air Hose To 5mm Tube Connector	XBFSC00054	56.0	21.0	55.0
Speed & length Counter	XBFSC00235	112 x 47 x 37		200.0
Airflow Gauge	XBFSC00278	210 x 27 x 50		250.0
24v dc Power Plug	XBFSC00283	135.0	50.0	150.0

Prysmian Telecom Cables & Systems UK Ltd, Chickenhall Lane, Bishopstoke, Hants SO50 6YU, UK

Technical Enquiries +44 (0) 2380 608760 Fax Number +44 (0) 2380 608769

© PRYSMIAN 2008. All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed correct at the time of issue. Prysmian reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian.

Issue Aug 2008  
Ref: SI010