

FDN - FTTH Distribution Node Joint

Prysmian Part Numbers: *See below*



The FDN - FTTH Distribution Node Joint is primarily used for the distribution of optical cables / blown fibres in both aerial and underground optical fibre networks. The joint is oval in shape, medium in size and offers high flexibility due to the cable entry options presented by the joint base. The single base configuration offers 58 round cable ports and, one oval port for loop through applications. The joint cover is fitted with a pressure release valve and the cap / base is sealed with an "O" ring and clamp mechanism. Cable entries can be sealed using mechanical cable entry kits (Cablelok™) on any of the ports and/or heatshrink sleeves on any of the larger ports.

Features and Benefits

- The FDN - FTTH Distribution Node Joint has a maximum capacity of 144 fibres (using standard heatshrink splice protectors)
- The joint is compatible with a large range of Prysmian manufactured optical cables including Zephyr™ mini blown cables, Rapier® micro-module cables and Sirocco® blown fibre.
- The large number of small diameter ports is ideal for the distribution of subscriber drops in FTTH networks and provides a critical flexibility point in the last mile network
- Upto 52 small diameter (1.7mm to 9.5mm) drop cables can be distributed from the closure

Kit Contents

The FDN - FTTH Distribution Node is supplied with splice trays and all accessories required for the complete installation of two cables. NOTE: Cablelok™ must be purchased separately to suit your cable diameter


Additional Items

- Splice Protectors
- Sealing Options
- Wall & Pole Mounting Bracket
- Installation Clamp / Mounting Bracket
- Loop-through Basket Kit
- Port Opening Tools

Technical Data


- Number of cable ports: 58 circular and 1 oval
- Maximum cable diameter (mm): 35 (see below)

Port Type	No. of ports	Cable Range (mm)	
		Cablelok™	Heatshrink
L	1	2 x 13.0 - 22.0	2 x 12.0 - 24.0
T	2	15.5 - 29.0	12.0 - 35.0
S	4	5.0 - 20.0	6.0 - 26.0
B	2	4.8 - 16.5	6.0 - 19.0
R	52	1.7 - 9.5	Not applicable



Refer to Datasheet HT006 for details on Cable Sealing options.

- Maximum number of splice trays: 12 standard
- Maximum fibre capacity of Joint:
 - 144 Using 2.4mm Heat Shrink (288 using SMF splice tray)
 - 216 Using 1.6mm Heat Shrink
 - 576 Using 12 Fibre Ribbon
 - 384 Using 4 Fibre Ribbon
 - 288 Using Mechanical Crimp
 - 96 Using Universal Mechanical
- Required space envelope (mm): (l) 455 x (w) 312 x (d) 222
- Operating temperature: -20°C to + 50°C (5 to 95% RH)



Part Numbers

FDN - FTTH Distribution Node

Part No.	No. of trays	Type of tray	Method of sealing
XJHSC00040	12	Ellipse SE-A Splice Tray	Cablelok™ sealing
XJHSC00041	12	Ellipse SE-A Splice Tray	Cablelok™ & Heatshrink sealing

Types of splice protector inserts and maximum splices for trays

Tray Type	Heat shrink (2.4mm) with Band	4-fibre Ribbon	Heat Shrink (1.6mm)	Mechanical Crimp	Universal Mechanical	12 Fibre Ribbon
Ellipse SE-B Splice Tray	12	32	18	24	8	48
Ellipse SMF Splice Tray	24					

Moulded Splice Fins	3A/PON Insert	6A Insert	Mechanical Crimp Insert	Ribbon Insert
---------------------	---------------	-----------	-------------------------	---------------

Prysmian Telecom Cables & Systems UK Ltd, Chickenhall Lane, Bishopstoke, Hants SO50 6YU, UK

Technical Enquiries +44 (0) 2380 608760 Fax Number +44 (0) 2380 608769

© PRYSMIAN 2007. All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed correct at the time of issue. Prysmian reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian.

Issue 01, June 2007
Ref: HT001

Additional Items

Cable Sealing

The ports of the FDN – FTTH Distribution Node Joint can be sealed using Cablelok™ (all ports) or heatshrink on the larger ports. Please see datasheet HT006 for further information.

Prysmian Part No. – see Datasheet HT006



Heat Shrink Splice Protectors

OAsys splice protectors are used to protect the fibre splice. They are 2.4mm in diameter and 45mm in length.

Prysmian Part No. - XPESC00031 (pack of 50)



Mechanical (Crimp) Splice Protectors

OAsys Mechanical Splice Protectors are used to protect the fibre splice. They are 45mm in length.

*Prysmian Part No. – XKTSC00078 (pack of 50)
- XKTSC00079 (pack of 12)*



Universal Mechanical Splice Protectors

OAsys Universal Mechanical Splice Protectors are used to splice fibres together without the need of a fusion splicing machine. They are 4mm wide x 4mm tall and 40mm in length. An assembly tool and splice holder is required for installation. See Prysmian data sheet AC007 for further information on mechanical splices.

Prysmian Part No. – XKTSC00121 (pack of 50)



Wall or Pole Mounting Bracket

The OAsys Joint Wall or Pole Mounting Bracket allows an OAsys FDN – FTTH Distribution Node Joint to be mounted vertically or horizontally on a pole, or against a wall face or bulk head. The bracket is secured using either screws or a steel band (not provided).

Prysmian Part No. – XHASC00083



Installation Clamp / Mounting Bracket

The Universal Installation Mounting Bracket or Clamp is designed for securing the closure in the horizontal or vertical position during installation of network cables or closure maintenance. The standard version will fit a number of closures including the FDN – FTTH Distribution Node Joint, plus there is an economy version specifically for this joint. Jaws for the universal unit can be purchased separately


*Prysmian Part Nos. – XHASC00078 (standard)
XHASC00081 (jaws only)
XHASC00083 (FDN economy version)*



Loop-through Basket Kit

The Loop-through Basket Kit enables the management of uncut fibre tubes in the joint.

Prysmian Part No. – XHASC00084



Port Opening Tools

Port Opening Tools are available in a number of sizes designed for the removal of the ends of closed joint cable entry ports. Three types are used on the FDN – FTTH Distribution Node Joint, depending upon port size (see below). A Coping Saw is required for larger ports.

*Prysmian Part Nos. – XHASC00071 (port size R)
XHASC00072 (port size B)
XHASC00073 (port size S)
XHASC00076 (coping saw – port sizes L & T)*



Prysmian Telecom Cables & Systems UK Ltd, Chickenhall Lane, Bishopstoke, Hants SO50 6YU, UK

Technical Enquiries +44 (0) 2380 608760 Fax Number +44 (0) 2380 608769

© PRYSMIAN 2007. All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed correct at the time of issue. Prysmian reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian.

The FDN joint is supplied to Prysmian under an OEM agreement by HellermannTyton. Cablelok™ is a HellermannTyton patented product. The Cablelok™ trademark is owned by HellermannTyton. Prysmian are an authorised distributor of these products and the use of the trademark.

Issue 01, June 2007
Ref: HT001