

UFC - Universal Fibre Joint

Prysmian Part Number: *See below*



Ellipse SE-A Splice Tray



Mass Splice Tray

The UFC - Universal Fibre Joint is a high capacity enclosure primarily used for local distribution of optical cables / blown fibres in both aerial and underground optical fibre networks. The joint is circular in shape and offers high flexibility due to the cable entry options presented by the joint base. The single base configuration offers 28 round cable ports together with two oval ports for loop through applications. The joint cover is fitted with a pressure release valve and has its cap / base sealed with an "O" ring and clamp mechanism. Cable entries can be sealed using either mechanical cable entry kits (Cablelok™) and/or heatshrink sleeves on all ports.

Features and Benefits

- The UFC - Universal Fibre Joint has a maximum capacity of 432 fibres (using standard heatshrink splice protectors)
- Can be supplied with the following tray options:
 - 6, 12, 18, 24, 30 or 36 Ellipse SE-A splice trays
 - 12, 24, 36, 48, 60 or 72 Ellipse SC splice trays
 - 4 Mass splice trays

The choice of tray will depend upon capacity, whether or not interchangeable splice inserts are required, number of tray entries and type of fibre and cable selected.

- The joint is compatible with a large range of Prysmian manufactured optical cables including Zephyr™ mini blown cables, Rapier® micro-module cable, Sirocco® blown fibre, mass link/fusion link ribbon fibre cables
- Can be used with high fibre count ribbon cables in super highway primary rings.
- With up to 26 small diameter ports (see overleaf for range of sizes) it is ideal for the distribution of subscriber drops in FTTH networks or for splicing in primary rings in metropolitan networks.
- Four different cover lengths depending upon number and type of tray selected.
- All Ellipse tray UFC - Universal Fibre Joints are fitted with loop storage baskets.

Kit Contents

The UFC - Universal Fibre Joint is supplied with splice trays and all accessories required for the complete installation of two cables. NOTE: Cablelok™ must be purchased separately to suit cable diameter


Additional Items

- Splice Protectors
- Sealing Options
- Wall & Pole Mounting Bracket
- Installation Clamp / Mounting Bracket
- Port Opening Tools
- Manifolds
- Adapters

Technical Data

- Number of cable ports: 28 circular and 2 oval
- Maximum cable diameter (mm): 35 (see below)

Port Type	No. of ports	Cable Range (mm)	
		Cablelok™	Heatshrink
L	1	2 x 13.0 - 22.0	2 x 12.0 - 24.0
LM	1	2 x 9.5 - 22.0	2 x 8.0 - 22.0
T	2	15.5 - 29.0	12.0 - 35.0
S	10	5.0 - 20.0	6.0 - 26.0
R	16	4.8 - 16.5	6.0 - 19.0



Refer to Datasheet HT006 for details on Cable Sealing options.

- Maximum number of splice trays: 36
- Maximum fibre capacity of Joint: See table below
- Required space envelope (mm): (l) 400 / 550 / 600 / 750 x (Ø) 310
- Operating temperature: -20°C to + 50°C (5 to 95% RH)

Cover

- A: 400mm length
- B: 550mm length
- BC: 600mm length
- C: 750mm length



Part Numbers

UFC - Universal Fibre Joint

Part No.	No. trays	Type of tray	Method of sealing	Cover	Standard		Special Products Available on request			
					HS 2.4	Mech	Mech	Universal	4F Ribbon	12F Ribbon
XJHSC00070	6	Ellipse SE-A Splice Tray	Cablelok™ sealing	A	72	N/A	144	48	288	288
XJHSC00071	12	Ellipse SE-A Splice Tray	Cablelok™ sealing	BC	144	N/A	288	96	576	576
XJHSC00072	18	Ellipse SE-A Splice Tray	Cablelok™ sealing	C	216	N/A	432	144	864	864
XJHSC00073	24	Ellipse SE-A Splice Tray	Cablelok™ sealing	C	288	N/A	576	192	1152	1152
XJHSC00074	30	Ellipse SE-A Splice Tray	Cablelok™ sealing	C	360	N/A	720	240	1440	1440
XJHSC00075	36	Ellipse SE-A Splice Tray	Cablelok™ sealing	C	432	N/A	864	288	1728	1728
XJHSC00076	6	Ellipse SE-A Splice Tray	Heatshrink sealing	A	72	N/A	144	48	288	288
XJHSC00077	12	Ellipse SE-A Splice Tray	Heatshrink sealing	BC	144	N/A	288	96	576	576
XJHSC00078	18	Ellipse SE-A Splice Tray	Heatshrink sealing	C	216	N/A	432	144	864	864
XJHSC00079	24	Ellipse SE-A Splice Tray	Heatshrink sealing	C	288	N/A	576	192	1152	1152
XJHSC00080	30	Ellipse SE-A Splice Tray	Heatshrink sealing	C	360	N/A	720	240	1440	1440
XJHSC00081	36	Ellipse SE-A Splice Tray	Heatshrink sealing	C	432	N/A	864	288	1728	1728
XJHSC00082	4	Mass Splice Tray	Cablelok™ sealing	C	576	N/A	1152	384	1536	2304
XJHSC00083*	4	Mass Splice Tray	Cablelok™ sealing	C	576	N/A	1152	384	1536	2304
XJHSC00084	4	Mass Splice Tray	Heatshrink sealing	C	576	N/A	1152	384	1536	2304
XJHSC00085*	4	Mass Splice Tray	Heatshrink sealing	C	576	N/A	1152	384	1536	2304
XJHSC00086	12	Ellipse SC Splice Tray	Cablelok™ sealing	A	96	96	N/A	N/A	N/A	N/A
XJHSC00087	24	Ellipse SC Splice Tray	Cablelok™ sealing	BC	192	192	N/A	N/A	N/A	N/A
XJHSC00088	36	Ellipse SC Splice Tray	Cablelok™ sealing	C	288	288	N/A	N/A	N/A	N/A
XJHSC00089	48	Ellipse SC Splice Tray	Cablelok™ sealing	C	384	384	N/A	N/A	N/A	N/A
XJHSC00090	60	Ellipse SC Splice Tray	Cablelok™ sealing	C	480	480	N/A	N/A	N/A	N/A
XJHSC00091	72	Ellipse SC Splice Tray	Cablelok™ sealing	C	576	576	N/A	N/A	N/A	N/A
XJHSC00092	12	Ellipse SC Splice Tray	Heatshrink sealing	A	96	96	N/A	N/A	N/A	N/A
XJHSC00093	24	Ellipse SC Splice Tray	Heatshrink sealing	BC	192	192	N/A	N/A	N/A	N/A
XJHSC00094	36	Ellipse SC Splice Tray	Heatshrink sealing	C	288	288	N/A	N/A	N/A	N/A
XJHSC00095	48	Ellipse SC Splice Tray	Heatshrink sealing	C	384	384	N/A	N/A	N/A	N/A
XJHSC00096	60	Ellipse SC Splice Tray	Heatshrink sealing	C	480	480	N/A	N/A	N/A	N/A
XJHSC00097	72	Ellipse SC Splice Tray	Heatshrink sealing	C	576	N/A	N/A	N/A	N/A	N/A

* Joint comes complete with loop storage basket

For special products, contact Prysmian sales office for part numbers

Types of splice protector inserts and maximum splices for trays

Tray Type	Heat Shrink (2.4mm) with Band	4-fibre Ribbon	Heat Shrink (1.6mm)	Mechanical Crimp	Universal Mechanical	12 Fibre Ribbon
Ellipse SE-A Splice Tray	12	32	18	24	8	48
Ellipse SC Splice Tray	8			8		
Mass Splice Tray	144	384	216	288	96	576

Moulded Splice Fins	3A/PON Insert	6A Insert	Mechanical Insert	Ribbon Insert
---------------------	---------------	-----------	-------------------	---------------

Prysmian Telecom Cables & Systems UK Ltd, Chickenhall Lane, Bishopstoke, Hants SO50 6YU, UK

Technical Enquiries +44 (0) 2380 608760 Fax Number +44 (0) 2380 608769

© PRYSMIAN 2007. All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed correct at the time of issue. Prysmian reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian.

Issue 02, June 2007
Ref: HT005

Additional Items

Cable Sealing

The ports of the UFC – Universal Fibre Joint Joint can be sealed using Cablelok™ or heatshrink on all ports. Please see datasheet HT006 for further information.



Prysmian Part No. – see Datasheet HT006

Heat Shrink Splice Protectors

OAsys splice protectors are used to protect the fibre splice. They are 2.4mm in diameter and 45mm in length. There is also a 1.6mm in diameter and 40mm in length for use with Ellipse SE-A and Mass splice tray.

Prysmian Part No. - XPESC00031 (pack of 50) 2.4mm X 45mm
- XHASC00014 (pack of 80) 1.6mm X 40mm



Mechanical (Crimp) Splice Protectors

OAsys Mechanical Splice Protectors are used to protect the fibre splice. They are 45mm in length.

Prysmian Part No. – XKTSC00078 (pack of 50)
- XKTSC00079 (pack of 12)



Universal Mechanical Splice Protectors

OAsys Universal Mechanical Splice Protectors are used to splice fibres together without the need of a fusion splicing machine. They are 4mm wide x 4mm tall and 40mm in length. An assembly tool and splice holder is required for installation. See Prysmian data sheet AC007 for further information on mechanical splices.

Prysmian Part No. – XKTSC00121 (pack of 50)



Wall or Pole Mounting Bracket

The OAsys Joint Wall or Pole Mounting Bracket allows an OAsys UFC – Universal Fibre Joint to be mounted vertically or horizontally on a pole, or against a wall face or bulk head. The bracket is secured using either screws or a steel band (not provided).

Prysmian Part No. – XHASC00086



Installation Clamp / Mounting Bracket

The Universal Installation Mounting Bracket or Clamp is designed for securing the closure in the horizontal or vertical position during installation of network cables or closure maintenance. The standard version will fit a number of closures including the UFC – Universal Fibre Joint, the jaws specific to this joint can be purchased separately.

*Prysmian Part Nos. – XHASC00078 (standard)
XHASC00081 (jaws only)*



Manifolds

A fibre manifold is a device for dividing and managing fibres within a splice closure or ODF. It consists of a moulded divider with snap-on cover with 1 or 2 polyethylene tubes inserted at one end and a number of similar tubes at the other.

Prysmian Part Nos.

Part No.	Inlet Tubes			Outlet Tubes			Manifold dimensions	
	No. of inlets	Bore Dia (mm)	Length (mm)	No. of outlets	Bore Dia (mm)	Length (mm)	W x H (mm)	Length (mm)
XHASC00001	1	4	75	4	3	1000	9.0 x 9.0	35.5
XHASC00002	1	4	1000	4	3	1500	9.0 x 9.0	35.5
XHASC00003	2	4	1000	6	3	1500	9.0 x 14.0	55
XHASC00004	2	3	1000	6	3	1500	9.0 x 14.0	55

4-Way Manifold



6-Way Manifold



Adapters

The application of an adapter is similar to a manifold except that it is fitted directly over the cable sheath (to 15mm outside diameter) with the unit tubes or groups of fibres being fed through flexible tubing or wrapped with spiral-cut tubing for loop-through applications. All kits are supplied with both types of tubing, cable ties and markers

*Prysmian Part Nos. – XHASC00005 (6 outlets, 4mm bore diameter)
XHASC00006 (12 outlets, 3mm bore diameter)
XHASC00007 (24 outlets, 3mm bore diameter)*



Port Opening Tools

Port Opening Tools are available in a number of sizes designed for the removal of the ends of closed joint cable entry ports. Three types are used on the UFC – Universal Fibre Joint, depending upon port size (see below). A Coping Saw is required for larger ports.

*Prysmian Part Nos. – XHASC00072 (port size B)
XHASC00073 (port size S)
XHASC00076 (coping saw – port sizes LM)*



Prysmian Telecom Cables & Systems UK Ltd, Chickenhall Lane, Bishopstoke, Hants SO50 6YU, UK

Technical Enquiries +44 (0) 2380 608760 Fax Number +44 (0) 2380 608769

© PRYSMIAN 2007. All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed correct at the time of issue. Prysmian reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian.

The UFC joint is supplied to Prysmian under an OEM agreement by HellermannTyton. Cablelok™ is a HellermannTyton patented product. The Cablelok™ trademark is owned by HellermannTyton. Prysmian are an authorised distributor of these products and the use of the trademark.

Issue 02, June 2007
Ref: HT005