

Sirocco Electric Compressor

Prysmian Part Number: See Table Below



The Sirocco Compressors are designed to deliver clean dry air for installing optical fibre using the blown fibre technique.

Both models (240v & 110v) feature quiet running, electrically driven rotary vane compressor units. These produce 100 l/min of pulse free treated compressed air at a working pressure of 10 bar. Together with their portability this makes them the ideal source of air for internal building optical fibre installations.

Features and Benefits

An air cooled aftercooler, reduces compressed air temperature to within 2°C of ambient and a 3-stage filtration system provides technically oil-free air.

These units are available with an optional 24Vdc outlet socket for supplying the blowing head (other voltages available on request).

Product Details

Model Ref.no.	Length (mm)	Width (mm)	Height (mm)	Output (l/min)	Pressure (bar)	Weight (kg)	Noise Level	Voltage
XBFSC00013	900	450	700	63	100	10	60dB(A) at 1m	240v-1ph-50hz
XBFSC00016	900	450	700	63	100	10	60dB(A) at 1m	110v-1ph-50hz

Prysmian Telecom Cables & Systems UK Ltd, Chickenhall Lane, Bishopstoke, Hants SO50 6YU, UK

Technical Enquiries +44 (0) 2380 608760 Fax Number +44 (0) 2380 608769

© PRYSMIAN 2005. All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed correct at the time of issue. Prysmian reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian.

Issue 01, October 2005
Ref: SR012