

FTTH Electric Compressor

Prysmian Part Number: XBFSC00318



The Sirocco Compressor is designed to deliver clean, dry air for installation of Blown Fibre units using compressed air. The Sirocco Compressor is a quiet, portable, electric motor driving a reciprocating compressor unit. Producing 60 l/min (0.06m³/min, 2.1 cfm) of treated compressed air at a maximum working pressure of 8 bar, it provides the ideal source of compressed air for the installation of blown fibre units for the FTTH market.

Due to the reduced air output and pressure the typical blowing distances of the Sirocco fibre units are reduced (2 & 4f – 500 mts, 8f – 400 mts, 12f – 350 mts). For tortuous routes this distance may be reduced further.

Features and Benefits

- The use of a cooling coil and large capacity air receiver reduces the compressed air temperature to within 2°C of ambient.
- A 3 stage filtration system provides technically oil-free air.
- IP Rating – 54.

Product Details

Length	Width	Height	Weight	Pressure	Output	Noise Level
400 mm	400 mm	800 mm	35 kgs	9 bar	60 l/min	59dB(A) @ 4mts

Prysmian Telecom Cables & Systems UK Ltd, Chickenhall Lane, Bishopstoke, Hants SO50 6YU, UK

Technical Enquiries +44 (0) 2380 608760 Fax Number +44 (0) 2380 608769

© PRYSMIAN Cables & Systems UK Ltd 2008. All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Cables & Systems UK Ltd. The information is believed correct at the time of issue. Prysmian Cables & Systems UK Ltd reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian Cables & Systems UK Ltd.

Issue 01 March 2008
Ref: SI011