

Compact Termination Box

Prysmian Part Number: *See Table Below*



The OAsys Compact Termination Box is designed for use in residential and business applications for the termination of up to four fibres. The wall box enables the installation of either a single Sirocco Blown Tube cable using up to a 4 fibre blown unit or two 2 fibre ruggedised cables to be spliced to four SC pigtails (PC or APC), which connect to adapters at the base of the unit.

The unit can be quickly installed within an office, house or communication room environment.

Features and Benefits

- Ergonomic design.
- Ability to allow cables to enter from rear or bottom of the unit.
- All fibres are positively managed to maintain a 30mm minimum bend radius.
- Optional Removable rear entry cable management.
- Flip tray to allow access to connectorised tails and cable entry.
- Compact, low profile, wall mounted unit used for small and large business premises.
- Removable cover for easy access.
- Tamperproof cover security screws available as an option.
- Unit manufactured from fire resistant UL94-V0 rated material.
- Patchcords exit unit on bottom face and are protected by two protection covers.
- Standard colour white. Other colours available on request.

Part Numbers

	Connector Type	
	SC/UPC	SC/APC
Empty	XCPSC00130	
1 Pigtail & 1 Adapter	XCPSC00233	XCPSC00235
2 Pigtails & 2 Adapters	XCPSC00092	XCPSC00096
3 Pigtails & 3 Adapters	XCPSC00234	XCPSC00236
4 Pigtails & 4 Adapters	XCPSC00093	XCPSC00097

Kit Contents

The OAsys Compact Termination Box is supplied with all of the components required to complete the installation of one Blown Fibre input cable, 4 splice protectors are supplied in the kit.

Additional Items

- None

Optional Items (if required as separate items)

- Patchcords
- Adapters
- Pigtails
- Security Screw Kit

Technical Data

- Number of input cable ports: 1
- Maximum input cable diameter (mm): 10mm
- Maximum Capacity: 4 Fibres
- Maximum no. of customer feeds: 4 Patchcords
- Required space envelope (mm): (l) 80 x (w) 120 x (d) 25
- Operating temperature: -20°C to + 50°C (5 to 95% RH)
- Material:-
 - Cap: FR High Impact Polystyrene
 - Base: FR High Impact Polystyrene
 - Splitter trays: FR High Impact Polystyrene
- Testing:-
 - Optical: Tested 1310,1550 & 1625nm
 - Dry heat: BS EN 60068-2-2 Test Bb
 - Damp heat: IEC 60068-2-3: 1969
 - Change of temperature: IEC 60068-2-14: 1984
 - Vibration: IEC 60068-2-6: 1995
 - Shock: IEC 60068-2-27: 1987

Logistics

- Packing Dimensions (mm): (l) 100 x (w) 150 x (d) 50
- Packed Weight (kg): 0.5
- Net weight (kg): 0.25
- Installation Instructions included

Pigtail Technical Data

Pigtails are supplied with either xx/UPC or xx/APC connectors.

xx/UPC connectors can be used in cases where xx/PC or xx/SPC connectors are required.

The standard fibre type supplied is G652 Single Mode. Please contact the sales desk if other fibre types are required.

	UPC	APC
• Insertion Loss (max)	0.3 dB	0.3 dB
• Return Loss (min)	50 dB	60 dB

Additional Items

Heatshrink Splice Protectors

OAsys splice protectors are used to protect the fibre splice. They are 2.2mm in diameter and 45mm in length.

Prysmian Part No. - XPESC00053 (pack of 50)
- XKTSC00050 (pack of 12)



Pigtails / Adapters / Patchcords

	SC / APC	SC / UPC
Adapter (duplex)	XPPSG00193	XPPSG00192
Pigtail (two colours)	XPPSC00249	XPPSC00247
Pigtail (four Colours)	XPPSC00250	XPPSC00248

Security Screw Kit

OAsys Security Screw Kit allows the installation of a tamper proof screw in order to stop any unwanted access in to the splicing area.

Prysmian Part No. – XCPSC00098
- (Security Tool XCPSC00099)



Prysmian Telecom Cables & Systems UK Ltd, Chickenhall Lane, Bishopstoke, Hants SO50 6YU, UK

Technical Enquiries +44 (0) 2380 608760 Fax Number +44 (0) 2380 608769

© PRYSMIAN 2005. All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed correct at the time of issue. Prysmian reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian.

Issue 05, June 2006
 Ref: WM001