

Oil & Gas - Cable Solutions

Exploration & Production - Offshore

Low Voltage & Control Cables

NEK 606 / IEC 60092-353

BU 0,6/1 kV BFOU/BFCU 0,6/1 kV

Low Voltage cables, fire retardant, fire resistant, low smoke, halogen free. Unarmoured/Armoured. Arctic Grade design option available on demand.

APPLICATION

Low Voltage & Control cables are used for fixed installations on ships and offshore platforms in a wide range of power supply and control applications. Prysmian offers a wide range of LV & Control cables with diverse design options depending on the reference standards and customer requirements.

STANDARDS & APPROVALS

NEK 606 Design guidelines

IEC 60092-350 Design guidelines

IEC 60092-351 Insulating material

IEC 60092-352 Choice and installation of electric cables

IEC-60092-353 Design guidelines

IEC 60092-359 Sheathing materials

IEC 60331-1,-2,-21 Fire resistance IEC 60332-1-2 Flame retardance

IEC-60332-3-22 Fire retardance

IEC-60754-1 Halogen free properties

IEC-61034-2 Smoke emission properties

on request

CSA 22.2 Cold bend/impact test at -40 °C /-35 °C

Det Norske Veritas-Germanischer Lloyd (DNV-GL) American Bureau of Shippings (ABS) Lloyds Register of Shipping (LRS) Bureau Veritas (BV) Russiam Maritime Register of Shipping (RMRS) RINa (Registro Italiano Navale)

DESIGN & CONSTRUCTION

CONDUCTOR

Tinned annealed copper conductor according to IEC 60228 cl. 2 (or cl.5 on request)

2 INSULATION

Mica tapes (s) +EPR or XLPE according to IEC 60092-360

BEDDING/INNER COVERING

(only armoured versions)

Flame retardant and halogen free thermoset compound

ARMOURING

(only armoured versions)

Tinned copper wire braid

Galvanized steel wire braid

OUTER SHEATH

Flame retardant, halogen free or halogen free and mud resistant thermoset compound, SHF2 (IEC 60092-360)

U P17

Halogen free

or **UP17 MUD**


Halogen free + mud resistant according to NEK TS 606

U P5

Halogen free

U P5/P12 MUD

Halogen free + mud resistant according to NEK TS 606





Oil & Gas - Cable Solutions

Exploration & Production - Offshore

Low Voltage & Control Cables

NEK 606 / IEC 60092-353

PERFORMANCES/RATINGS





IIEC 60332-3-22 IEC 60331-1,-2,-21

CHEMICAL RESISTANCE



EXCELLENT (MUD RES)

IMPACTS









MIN. PERMISSIBLE AMBIENT TEMPERATURE



(-40°C for Arctic Grade)

MAX OPERATING



+90 °C

SHORT CIRCUIT



+250 °C



COOD

QUALITY & TESTING

Prysmian has a built-in multi-step quality assurance program, covering the production process from cable design and raw material purchases to final inspection and testing documentation.

The ISO 9001 quality system of Prysmian Group (together with ISO 14001 and OHSAS 18001) has been assessed, approved and is currently audited by SGS.

This product information sheet is provided for reference only.

Please consult the factory or your representative to confirm all engineering information or refer to the related catalogues available in the local countries website.

