



# D10e: UC<sup>FIBRE™</sup> Duplex cord 2x2.0 mm

Assembly cable with 2 ES9 buffered fibres, aramid yarn, FireRes<sup>®</sup> sheath. VDE: J-V(ZN) H 2



Dca  
CPR

Eca  
CPR

## Application and installation

Interconnect cabling

This cable features Draka's ES9 easy strippable tight buffer

Patch cord cable, very well suited for mounting small form factor connectors

Internal wiring

## Standards

EN 187 000, IEC 60794-2, IEC 60794-2-10, ISO 11801-1, EN 50 173-1

## Flame resistance

LSHF-FR (FRNC): IEC 60332-1-2; IEC 60332-3-24; IEC 60754-2; IEC 61034; EN 50399 Class D<sub>ca</sub>s2d2a1, Class E<sub>ca</sub>

## Construction

Fibre	2 ES9 easily strippable tightly buffered fibres 900 µm ± 50 µm	
Fibre colours	Fibre 1	White or Natural
	Fibre 2	Blue
Strength member	Ultra high modulus aramid yarns	
Sheath	Halogen free, flame resistant thermoplastic sheathing compound acc. to EN 50290-2-27, UV stabilised	
Sheath colours	Cable with Singlemode	Yellow, RAL 1018
	Cable with MaxCap-BB-OM3	Aqua, RAL 6027
	Cable with MaxCap-BB-OM4	Erika-Violet RAL 4003
	Cable with BendBright WideCap-OM5	Lime-Green
Sheath marking	Draka UC <sup>FIBRE</sup> I T LSHF-FR Dca-s2-d2-a1 ES9 2.0 2<Fibre type><Fibre brand><Item No><factory code><Batch Number><Meter mark> J-V(ZN)H 2 <Fibre family> <Mode field diameter> /125 <Transmission Class> G <fibre count> <Mode field diameter>/125 AXAI-I/P-20	

# D10e: UC<sup>FIBRE™</sup> Duplex cord 2x2.0 mm

## Physical properties

IEC 60794-1-21/22

Attribute	Method	Limits
Nominal dimensions	-	2.0 mm x 4.2 mm
Nominal weight	-	8.0 kg/km
Tensile strength (dynamic)	E1	300 N (fibre strain ≤ 0.5%)
Tensile strength (permanent)	E1	150 N (fibre strain ≤ 0.25%)
Compressive strength (crush)	E3	3000 N
Impact	E4	1 Nm; R = 12.5 mm
Torsion	E7	5 cycles ± 1 turn
Min. Bending radius	E11	R = 20 mm
For version with BendBright <sup>XS</sup> fibre: Min. Bending radius	E11	R = 7.5 mm R = 15 mm, 6 turns around a mandrel ø 30 mm (maximum attenuation increase ≤ 0.02 dB at 1550 nm). Maximum attenuation increase for R = 10 mm 0.1 dB/turn at 1550 nm. Maximum attenuation increase for R = 7.5 mm 0.5 dB/turn at 1550 nm.
Temperature range	F1	Operation and installation: -40°C to 70°C. Storage: -40°C to 70°C
Heat of combustion	-	180 MJ/km 0.05 kWh/m

## Product codes – ordering information

Product code	DoP Number*	Product description	Fibre count	Fibre type	Fibre data sheet
60019443		UC <sup>FIBRE™</sup> I T LSHF-FR ES9 2.0 2 OM2B	2	MaxCap-BB-OM2	C34
60019444		UC <sup>FIBRE™</sup> I T LSHF-FR ES9 2.0 2 OM3B	2	MaxCap-BB-OM3	C31
60040436		UC <sup>FIBRE™</sup> I T LSHF-FR ES9 2.0 2 OM4B	2	MaxCap-BB-OM4	C32
		UC <sup>FIBRE™</sup> I T LSHF-FR ES9 2.0 2 OM5B	2	WideCap-OM5	C39
60019289		UC <sup>FIBRE™</sup> I T LSHF-FR ES9 2.0 2 SM2D.P	2	OS2 – G.652.D – tight geometry	C18
		UC <sup>FIBRE™</sup> I T LSHF-FR ES9 2.0 2 SM7A1.P	2	OS2 – BendBright G.657.A1 – tight geometry	C38
60019442		UC <sup>FIBRE™</sup> I T LSHF-FR ES9 2.0 2 SM7B	2	OS2 – BendBright <sup>XS</sup> G.657. A2	C24
		UC <sup>FIBRE™</sup> I T LSHF-FR ES9 2.0 2 SM7B.P	2	OS2 – BendBright <sup>XS</sup> G.657. A2 – tight geometry	C25

\*DoP Numbers are per product code and any DoP number proves CPR approval for the cable. DoP files can be downloaded from the website: [www.prysmiangroup.com/cpr](http://www.prysmiangroup.com/cpr)

© PRYSMIAN GROUP 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.