


D24: UC^{FIBRE™} 4-Fibre Break-out Cable

**Indoor, flexible, break-out cable with 4 ES9 tightly buffered fibres, aramid yarn, FireRes® sheath.
VDE: J-V(ZN)HH 4**



Application and Installation

Interconnect cabling
LAN horizontal cabling
Patch cord cable
Short distance data-, control- and video transmission
Internal wiring in data centres

Standards

EN 187 000, IEC 60794-2, IEC 60794-2-10, ISO 11801-1, EN 50 173-1

Flame Resistance

LSHF-FR (FRNC): IEC 60332-1-2; IEC 60332-3-24, IEC 60754-2; IEC 61034; EN 50399 Class D_{ca}s2d2a1; Class E_{ca}

Construction

ø2.1 mm unit	ES9 tightly buffered fiber 900 µm ± 50 µm Aramid yarn strength member LSZH sheath, in the same colour as the outer sheath, marked with unit number	
4 units	Stranded together	
Ripcord	Polyester	
Sheath colours	Cable with SM fibres: BendBrightXS G.657.A2, BendBright G.657.A1	Yellow, RAL 1018
	Cable with M6-OM1	Grey, RAL 7037
	Cable with MaxCap-BendBright-OM2	Orange, RAL 2009
	Cable with MaxCap-BendBright-OM3	Aqua, RAL 6027
	Cable with MaxCap-BendBright-OM4	Erika-Violet, RAL 4003
	Cable with BendBright WideCap-OM5	Lime-Green
Sheath	Halogen free, flame resistant thermoplastic sheathing compound acc. to EN 50290-2-27, UV stabilised	
Sheath marking	Draka UC ^{FIBRE} I B LSHF-FR Dca s2d2a1 ES9 2.1 4 <Fibre type><Fibre brand><Item No><factory code><Batch Number><Meter mark> J-V(ZN)HH 4 <Fibre family> <Mode field diameter> /125 <Transmission Class>	

D24: UC^{FIBRE}TM 4-Fibre Break-out Cable

Physical Properties

IEC 60974-1-21/22

Attribute	Method	Limits	
Fibre count		4	
Nominal diameter [mm]	-	6.5 (the cable is not completely round)	
Nominal weight [kg/km]	-	30	
Maximum installation load (a few hours) [N]	-	-	
Short term tensile strength (some days) [N]	E1	850	
Permanent tensile strength [N]	E1	425	
Impact [J]	E4	10, R= 12.5 mm	
Crush (compressive strength)	E3	3000 N/ 100 mm	
Torsion	E7	5 cycles ± 1 turn	
Minimum bending radius	E11	20 mm	
Minimum bending radius under tension	E18A	-	
Temperature range	F1	Operation and installation	-20 °C to 60 °C
		Storage	-20 °C to 70 °C
Minimum bending radius of the 2.1 mm units	G01	With standard fibres	20 mm
		With MaxCap-BB-OMx fibres	7.5 mm
		With BendBright-XS fibers:	7.5 mm
Heat of combustion [MJ/km] – [kW/m]			510
			0.14

Product Codes

Product code	DoP Number*	Product description	Fibre count	Fibre type	Fibre data sheet
60019470	1004766	UC ^{FIBRE} I B LSHF-FR ES9 2.1 4 OM2B	4	OM2 MaxCap-BB-OM2	C34
60019582	1003961	UC ^{FIBRE} I B LSHF-FR ES9 2.1 4 OM3B	4	OM3 MaxCap-BB-OM3	C31
60028719		UC ^{FIBRE} I B LSHF-FR ES9 2.1 4 OM4B	4	OM4 MaxCap-BB-OM4	C32
60019450		UC ^{FIBRE} I B LSHF-FR ES9 2.1 4 SM2D	4	OS2 – G.652.D	C03
60019451	1004765	UC ^{FIBRE} I B LSHF-FR ES9 2.1 4 SM7B	4	OS2 - BendBright XS G.657.A2	C24
60030934		UC ^{FIBRE} I B LSHF-FR ES9 2.1 4 SM7B.P	4	OS2 - BendBright XS G.657.A2	C25

*DoP Numbers are per product code and any DoP number proves CPR approval for the cable. DoP files can be downloaded from the website: www.prysmiangroup.com/cpr

© PRYSMIAN GROUP 2017, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.