






Multicore high temperature airframe cables (260°) EN2267-007/ PN - QL - RK series

Design	Draka Fileca part number	Stranding (n x mm)	Nb of cores	Conductor		Diameter cores max (mm)	Max (Ω/km) (at 20°C) R. max	Max weight (g/m)
				Gauge	Section (mm²)			
	F EN2267-007B001P	19 x 0.10	2	26	0.15	0.97	165.0	5.03
	F EN2267-007B002P	19 x 0.12	2	24	0.21	1.04	117.0	6.31
	F EN2267-007B004P	19 x 0.15	2	22	0.34	1.19	61.7	9.03
	F EN2267-007B006P	19 x 0.20	2	20	0.60	1.53	34.1	15.75
	F EN2267-007B010P	19 x 0.25	2	18	0.93	1.82	21.7	23.93
	F EN2267-007B012P	19 x 0.30	2	16	1.34	2.22	14.9	34.55
	F EN2267-007B020P	37 x 0.25	2	14	1.82	2.49	11.2	46.16
	F EN2267-007B030P	37 x 0.32	2	12	2.98	2.97	6.99	68.62
	F EN2267-007B051P	61 x 0.32	2	10	4.91	3.61	4.22	108.1
	F EN2267-007B090P	127 x 0.30	2	8	9	4.77	2.37	194.8
PN series	F EN2267-007B140P	27 x 7 x 0.30	2	6	13.4	6.30	1.63	290.18
	F EN2267-007C001P	19 x 0.10	3	26	0.15	0.97	165	7.55
	F EN2267-007C002P	19 x 0.12	3	24	0.21	1.04	117	9.5
	F EN2267-007C004P	19 x 0.15	3	22	0.34	1.19	61.70	13.6
	F EN2267-007C006P	19 x 0.20	3	20	0.60	1.53	34.1	23.7
	F EN2267-007C010P	19 x 0.25	3	18	0.93	1.82	21.7	35.99
	F EN2267-007C012P	19 x 0.30	3	16	1.34	2.22	14.9	51.96
	F EN2267-007C020P	37 x 0.25	3	14	1.82	2.49	11.2	68.43
	F EN2267-007C030P	37 x 0.32	3	12	2.98	2.97	6.99	103.21
	F EN2267-007C051P	61 x 0.32	3	10	4.91	3.61	4.22	162.65
	F EN2267-007C090P	127 x 0.30	3	8	9	4.77	2.37	293.03
QL series	F EN2267-007C140P	27 x 7 x 0.30	3	6	13.4	6.30	1.63	435.26
	F EN2267-007D001P	19 x 0.10	4	26	0.15	0.97	165	10.07
	F EN2267-007D002P	19 x 0.12	4	24	0.21	1.04	117	12.72
	F EN2267-007D004P	19 x 0.15	4	22	0.34	1.19	61.70	18.18
	F EN2267-007D006P	19 x 0.20	4	20	0.60	1.53	34.1	31.7
	F EN2267-007D010P	19 x 0.25	4	18	0.93	1.82	21.7	48.18
	F EN2267-007D012P	19 x 0.30	4	16	1.34	2.22	14.9	69.56
	F EN2267-007D020P	37 x 0.30	4	14	1.82	2.49	11.2	92.96
	F EN2267-007D030P	37 x 0.32	4	12	2.98	2.97	6.99	138.18
	F EN2267-007D051P	61 x 0.32	4	10	4.91	3.61	4.22	217.77
	F EN2267-007D090P	127 x 0.30	4	8	9	4.77	2.37	392.32
RK series	F EN2267-007D140P	27 x 7 x 0.30	4	6	13.4	6.30	1.63	580.35

Passing and / or copying of the document, use or communicate of its content is not permitted without prior authorization. Information subject to change without notice.

Ref.: A 175 - © - 2000 - Médiasquare



Draka Fileca
Member of Draka France