


## ICS IE UC900 SS27 Cat.7 PUR

**IE S/FTP patch cable 4x2xAWG27/7 with abrasion and oil resistant PUR sheath**



### Application

Work area and patch cord cable  
IEEE 802.3: 10Base-T; 100Base-T; 1000Base-T; 10GBase-T  
IEEE 802.5 16 MB; ISDN; TPDDI; ATM

### Standards

EIA/TIA 568A;  
ISO/IEC 11801 2<sup>nd</sup> ed.; IEC 61156-6  
EN 50173-1; EN 50288-4-2

### Flame resistance

IEC 60332-1; IEC 60754-2; IEC 61034

### Chemical resistance

Oil resistant against Mineral – oil, ASTM – oil  
The sheath material is tested in Hydraulic oil  
ARAL VITAM 32, Mobil DTE 13 M, Gear oil ARAL DEGOL BG Plus 320 and Tribol 1710/320.

### Construction

Conductor	stranded bare copper wires, Ø 0.42 mm (AWG 27/7)
Insulation	foam-skin Polyethylene, Ø 0.98 mm
Twisting	2 cores to the pair
Pair screen	Al-laminated plastic foil
Cable lay up	4 pairs (PiMF) to the core
Screen	copper braid, tinned
Sheath	PUR
Colour	red
Marking	DRAKA UC900 SUPER SCREEN 27 CATEGORY 7 S/FTP Patch 4P IEC 61156-6 PUR, batch number and meter marking

# ICS IE UC900 SS27 Cat.7 PUR

## Mechanical properties

Bending radius	without load	≥ 25 mm
	with load	≥ 50 mm
Temperature range	during operation	-35°C to + 75°C
	during installation	-5°C to + 50°C
UV resistance of sheath material		acc. to IEC60068-2-5
Ozone resistance		acc. to EN 60811-2-1, clause 8
Smoke density		acc. to EN 50268-2, IEC61034-1 and 2
Corrosivity		acc. EN 50267-1 and 2, IEC 60754-1 and 2

## Electrical properties

at 20°C ± 5°C

Loop resistance		≤ 340 Ω/km
Resistance unbalance		≤ 3%
Insulation resistance	(500 V)	≥ 2000 MΩ*km
Mutual capacitance	at 800 Hz	Nom. 43 nF/km
Capacitance unbalance	(pair/ground)	≤ 1500 pF/km
Characteristic impedance	(1-100 MHz)	(100 ± 15) Ω
	(100 - 250) MHz	(100 ± 18) Ω
	(250 - 600) MHz	(100 ± 25) Ω
Nominal velocity of propagation		ca. 79 %
Propagation delay		≤ 427 ns/100m
Delay skew		≤ 12 ns/100m
Test voltage	(DC, 1 min) core/core and core/screen	1000 V
Transfer impedance	at 1 MHz	25 mΩ/m
	at 10 MHz	15 mΩ/m
	at 30 MHz	30 mΩ/m
Coupling attenuation		75 dB

## Electrical data (nominal)

acc. to Cat.7 (at 20°C)

F (MHZ)	Attenuation (dB/10m)	NEXT (dB)	PS-NEXT (dB)	ACR (dB/100m)	ELFEXT (dB/100m)	PS-ELFEXT (dB/100m)	Return loss (dB)
1.0	0.3	90	87	90	80	77	23
4.0	0.6	90	87	89	80	77	24
10.0	1.0	90	87	89	80	77	25
16.0	1.3	90	87	89	76	73	25
20.0	1.4	90	87	89	74	71	25
31.2	1.8	90	87	88	70	67	25
62.5	2.6	90	87	87	64	61	23
100.0	3.2	87	84	84	60	57	21
125.0	3.6	85	82	81	58	55	20
155.5	4.0	84	81	80	56	53	19
175.0	4.3	83	80	79	55	52	19
200.0	4.6	82	79	77	54	51	18
250.0	5.1	81	78	76	52	49	18
300.0	5.6	80	77	74	50	47	17
450.0	6.9	77	74	70	47	44	17
600.0	7.9	75	72	67	44	41	17
750.0	8.7	73	70	64	42	39	
900.0	9.7	72	69	62	41	38	
1000.0	10.2	71	68	61	40	37	

## ICS IE UC900 SS27 Cat.7 PUR

### Technical data

Part number	Cable type DIN/VDE	Product name	Colour	Outer diameter mm	Fire load		Weight kg/km	Copper content	Tensile force N
					MJ/km	kWh/m			
1001136	Li-02YSC11Y 4x2x0.42L PIMF	UC900 SS27 Cat.7 PUR S/FTP 4P	red	5.9	383	0.106	34	24	100

### Product Code Table

Product Description	Product Code	PG Reference Code	PG Part Number
UC900 SS27 C7 S/FTPp 4P PUR RD 500DW	1001136-00500DW	60014327	<b>60011459</b>
UC900 SS27 C7 S/FTPp 4P PUR RD	1001136	60014327	<b>60014327</b>
UC900 SS27 C7 S/FTPp 4P PUR RD 100RW	1001136-00100RW	60014327	<b>60014328</b>
UC900 SS27 C7 S/FTPp 4P PUR RD 1000DW	1001136-01000DW	60014327	<b>60014330</b>

© PRYSMIAN GROUP 2011, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.