



Exploration & Production

Downhole Cables

TEC (Instrumentation and Power Cables)

SPECIALTY TEC: LARGE DIAMETER TEC

TEC - Tubing Encased Cable (TEC) is designed and manufactured to withstand the varying harsh environments found associated with the oil and gas industry. The cable can be utilized for data transmission such as downhole gauge application through to larger cores where power is required or a combination of both.

APPLICATION

Large Diameter TEC's can have larger conductor cross-sections than STANDARD TEC and typically have higher power ratings.

STANDARDS & APPROVALS

Advanced Well Equipment Standard
Group AWES Recommended Practice for
Qualification of Tubing Encapsulated Conductor
AWESTEC_01

QUALITY & TESTING

Manufactured in accordance with standard
Inspection and Quality Plans
Downhole cables are manufactured according
to applicable ASTM standards for each specific
material:

- Alloy 825: ASTM B704 and B751
- Stainless Steel 316L: ASTM A450 and A632

The pressure ratings of TEC are based on
the collapse pressure of the 1/4" tube, not
burst pressures normally associated with
capillary tubes. The collapse (yield) pressure is
calculated using API Bulletin 5C3 Formula # 1 -
Yield Strength Collapse Pressure Formula

DESIGN & CONSTRUCTION

- Temperature ranges up to 260°C
- Outer tube is tig welded and drawn through a die to final size
- Centralized conductor
- Application Specific
- Double Extruded Filler
- Optional Bumper Bars
- Custom Line Marking
- Safety-Strip® Encapsulation
- Continuous Length up to 100,000 ft.

Outer Tube Materials

- 316L Stainless Steel (UNS 31603)
- A825 Alloy (UNS N08825)

Outer Tube Sizes

- 3/8" to 5/8"

Double Extruded Centralized Core

- Size : 4 AWG - 28 AWG
- Type: Solid or Stranded Conductor
- Plating (if required): Tin, Nickel, or Silver plating

Encapsulation (Optional)

- PP (Polypropylene) / TPR (Santoprene) /
PA (Nylon) / PVDF / ETFE (Tefzel) / ECTFE
(Halar) /FEP / PFA / ECA 3000
- Round or Square profile

Pressure Rating

- 3/8" up to 20Kpsi
- 5/8" up to 10Kpsi

