


Equipment cables

24 x 2 x 0.4 mm cables

Cable design

EMI/RFI shielded, halogen free plastic compound insulated and sheathed multi-twisted pair
26 AWG (0.4 mm) cables



- 1) Four screened 24-pair bundles
- 2) Manufacturer identification thread
- 3) Non-metallic rip cord (if required)
- 4) Outer LSOH sheath

Cable construction 24 x 2 x 0.4 mm (PRYSMIAN CODE 5002499)

Conductor:	Annealed solid copper wire Diameter 0.40 ± 0.01 mm (AWG 26)
Insulation:	Halogen free polyethylene compound Minimum thickness: 0.13 mm Nominal diameter: 0.74 mm
Cabling element:	Pairs with lay length ≤ 75 mm
Colour code:	According to IEC Publication 189/2, Appendix A and IEC Publication 304
Stranding of pairs:	Stranding of 24 pairs to form a compact and circular bundle
Wrapping tape:	One or more synthetic tapes
Screen:	AL / PET tape (aluminium thickness ≥ 0.05 mm)
Identification units:	Colored tapes (blue-orange-green-brown)
Braid wire:	Tinned copper wire, diameter ≥ 0.10 mm ≤ 0.20 mm Coverage $\geq 50\%$
Cable core:	Stranding of four screened 24 pair bundles
Rip cord:	Non-metallic rip cord (if required)
Identification thread:	PRYSMIAN thread (green/brown)
Outer sheath:	Low smoke halogen free (LSOH) flame retardant thermoplastic compound (Grey RAL7032) Minimum thickness: 0.75 mm
Outer cable diameter:	23.5 mm

© PRYSMIAN GROUP 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.

Equipment cables

24 x 2 x 0.4 mm cables

Sheath marking

PRYSMIAN (x) - aaaa

x = factory code
aaaa = production year (es. 2012)

Interval: 300 mm
Color: blue or black

Electrical data at 20°C

D.C. electrical resistance of each conductor:	≤ 146.8 Ohm / Km
Voltage test for 1 minute:	1000 V a.c. or 1500 V d.c.
Insulation resistance:	Min. ≥ 1000 Mohm*km
Maximum mutual capacitance (500÷2000 Hz):	≤ 100 nF/km
Capacitance unbalance: pair to earth:	99% values ≤ 750 pF/500 m 100% values ≤ 1500 pF/500 m
Attenuation:	≤ 33 dB/km @ 1 MHz ≤ 110 dB/km @ 10 MHz
Near-end and Far-end crosstalk:	≥ 55 dB @ 1 MHz ≥ 40 dB @ 10 MHz
Impedance:	100±15 ohm @ 1 and 10 MHz
Transfer impedance:	@ 30 MHz 11 mohm/m @ 100 MHz 36 mohm/m @ 300 MHz 110 mohm/m @ 1000 MHz 360 mohm/m

Fire performance

Flammability (single cable) according to IEC 60332-1

© PRYSMIAN GROUP 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.