

SiroccoXS Petrol Compressors

Part Numbers: XBFSC00002



The Sirocco Compressor is designed to deliver clean, dry air for installation of optical fibre using the blown fibre technique.

The Sirocco blown fibre compressor is a portable, petrol engine driven rotary vane compressor unit. Producing 120 l/min of pulse free treated compressed air at a working pressure of 10 bar, it provides the ideal source for field installation of blown fibre units.

An extremely reliable Honda GX240QX OHV Petrol Engine provides power for the compressor.

Features and Benefits

- The unit incorporates a 12Vdc air cooled aftercooler reducing the compressed air temperature to within 2°C of ambient.
- A 3-stage filtration system provides technically oil-free air.
- The unit is supplied with a 24Vdc-outlet socket which provides the power supply to the blowing head.

Product Details

Model Ref. No.	Length (mm)	Width (mm)	Height (mm)	Output (l/min)	Pressure (bar)	Weight (kg)	Noise Level
XBFSC00002	900	500	750	120	10	85	62dB(A) at 1m