

Wall Mounted Cabinets

Prysmian

A Brand of Prysmian Group

Product code – See table below



DESIGN & CONSTRUCTION

- Mild steel construction powder coated in RAL7035
- Maximum load capacity of 100kgs
- Single point lock
- Shatterproof smoked glass door
- Lockable and removable side panels

Product description

A range of strong and robust 19" Wall Mounted Cabinets. The cabinets are fully vented with a lockable steel framed glass door for safety and security. Quick release hinges allow for easy access to the cabinet for loading equipment and cables. Removable side panels allow access from each side and gland plate covers and cable strain relief positions are included in the top and bottom of the cabinets. The cabinets are available in a range of sizes from 7U up to 20U.

Technical data

Part Number	Height (U)	Width x Depth (mm)	Packing Dims (mm)	Weight (Kg)	Weight Packed (Kg)
XCPSC03904	7	600x450	660x520x480	14.5	17
XCPSC03905	7	600x600	650x650x480	18	21
XCPSC03906	9	600x450	660x520x480	17.6	20.2
XCPSC03907	9	600x600	650x650x480	22	25
XCPSC03908	12	600x450	660x520x480	22.5	25
XCPSC03909	12	600x600	650x650x480	28	31
XCPSC03910	16	600x450	660x520x480	29	32
XCPSC03911	16	600x600	650x650x480	26	39.5
XCPSC03912	20	600x450	660x520x480	35	38
XCPSC03913	20	600x600	650x650x480	43	46.5

Wall Mounted Cabinets


Prysmian

A Brand of Prysmian Group

Main characteristics

Kit Contents

Wall mounted cabinets are supplied with side panels left and right, a set of 19" mounting rails, cage nuts and a lockable glass door.



Additional Items


Ringed Cable Bars

Ringed cable bars are 19" panels that allow cables to be passed from one side of the cabinet to the other side. They are available in a number of sizes.

Prysmian Part Nos: -

XCPSC00798 – 1U 4 Ring Cable Bar

XCPSC00799 – 2U 4 Ring Cable Bar



Blank Panels

Blank panels are 19" panels that can be mounted in the cabinet to blank off any unused space. They help with airflow in cases where active equipment is used.

Prysmian Part Nos: -

XCPSC00801 – 1U Blank Panel

XCPSC00802 – 2U Blank Panel

XCPSC00803 – 3U Blank Panel



Brushed Panel

The brushed panel is a 19" panel fitted with a brush, to enable patchcords to be routed from the front of the cabinet to the back of the cabinet. It helps with airflow in the cabinet in cases where active equipment is used.

Prysmian Part Nos.: - XCPSC00804 – 1U Brush Strip



Adjustable feet and castors

The adjustable feet and castors can be fitted to the cabinets prior to the installation. The adjustable feet come as a pack of 4 PVC with an M10 single point fixing, the castors are supplied with four wheels two of which contain brakes. Both the castors and feet have a maximum load rating of 25Kg.

Prysmian Part Nos.: -

XCPSC03914 – Feet kit

XCPSC03915 – Wheel kit



Wall Mounted Cabinets

Prysmian

A Brand of Prysmian Group

Additional Items Cont.

19" Power Distribution Units

The 19" power Distribution Units can be supplied with 13A UK Sockets or 16A IEC C13 Sockets. Each unit contains 6 power outlets and are CE approved, each unit has a 2.5M cable.



Prysmian Part Nos.: -

XKTSC01465 – 6 way UK

XKTSC01456 – 6 way IEC C13

Fan Kits

1 or 2 fan units can be fitted into the cabinets, fans have power switch and include a thermostat and power lead, fan kits are used to provide cooling in cases where active equipment is used.



Prysmian Part Nos. –

XKTSC01467 – 1 fan kit

XKTSC01468 – 2 fan kit

Please contact your local sales office listed on www.prysmiangroup.com

© Prysmian Group 2020, All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.