

Small Distribution Wall Box (SDWB)

Prysmian Part Numbers: See below



The Small Distribution Wall box is a wall mounted product used for the distribution of fibres to up to six customer drop cables. Each customer has an individual splice tray that can house up to four splices. The box also has the added feature of a built in figure of eight routing system, that prevents fibre movement when aerial input cables are subjected to ice and wind loading. The unit is supplied with a gas/water block for the input cable. The box can be supplied in white or dark grey and has a sealing rating of IP55. Customer drop cables of 3 to 6mm can be distributed from the box.

Features and Benefits

- Can be supplied in white or dark grey.
- Each box comes with three double splice trays (6 customer trays) pre-fitted, and a single element splice tray for spare fibre storage.
- The box is supplied with a Gas/water block connector for use with blown fibre input cables and a 6-6mm reducer and 3mm transport tube.
- All fibres are positively managed to maintain a 30mm minimum bend radius within the wall box.
- A unique figure of eight locking system is integrated into the box. This prevents movement of fibres from aerial input cables when subjected to ice and wind loading.
- The box is sealed to IP55.
- Splice trays hinge upwards individually, allowing full access to spliced fibres without disturbance to live fibres in adjacent trays.
- The wall boxes come with everything required to install one input cable and up to six drop cables (only splice protectors to be ordered separate)
- Storage area inside the box to hold any unused output cable sealing grommets.
- The boxes are UV stable to prevent discolouration of the material. The boxes are manufactured from UL94-V0 rated materials.

Kit Contents

The SDWB is supplied with
 3 x Customer Splice Tray (6 trays).
 1 x Single Element Splice Tray
 1 x Wall fixing Kit
 1 x Installation Guide
 6 x Drop Sealing Grommet.
 7 x Cable Ties
 1 x M20 Entry Cable Gland
 1 x Aerial Cable Locking Kit

Additional Items

- Splice protectors

Part Numbers

- **XCPSC01915** – White 6FDP
- **XCPSC01916** – Dark Grey 6FDP

Technical Data

• Number of cable ports:	1 input, 6 output
• Maximum cable diameter (mm):	18 Input, 3-6 Output
• Maximum number of splice trays:	6 Customer Trays (24 fibre) 1 Single Element Tray (for storage)
• Required space envelope (mm):	(w) 220 x (h) 150 x (d) 50.
• Operating temperature:	-20°C to + 50°C (5 to 95% RH)
• Material:-	
• Box:	FR ABS Dark Grey (RAL7030) or FR ABS White (RAL9016)
• Splice trays:	FR ABS White (RAL9016)
• Testing:-	
• Sealing:	IP55
• Optical:	Tested 1310nm,1550nm and 1625nm
• Dry heat:	BS EN 60068-2-2 Test Bb
• Damp heat:	IEC 60068-2-3: 1969
• Change of temperature:	IEC 60068-2-14: 1984
• Vibration:	IEC 60068-2-6: 1995
• Shock:	IEC 60068-2-27: 1987

Logistics

• Packing Dimensions (mm):	(w) 230 x (h) 160 x (d) 60
• Packed Weight (Kg):	0.55
• Net Weight (Kg):	0.5
• Installation Instructions Included	

Additional Items

Heat Shrink Splice Protectors

Splice protectors are used to protect the fibre splice. They are 1.3mm in diameter and 30mm in length.



Prysmian Part No. - XPESC00057 (pack of 50)

Please contact your local sales office listed on www.prysmiangroup.com

© Prysmian Group 2013, All Rights Reserved.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed correct at the time of issue. Prysmian Group reserves the right to amend this specification without notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.