


S-2YCCYY 8 x 0.6/3.7D – 75 Ω PVC

Coaxial SDH-Switch Board Cables acc. to Belgacom TR-SP.
 109-8



Application

Standards

acc. to Belgacom specification TR-SP. 109-8

Flame resistance

Construction

Inner conductor	copper wire, bare, diameter 0.60 mm ± 0.03 mm
Insulation	PE 3.75 mm ± 0.10 mm
1 st outer conductor	copper braid, bare
2 nd outer conductor	copper braid, bare
Sheath	PVC 6.7 mm ± 0.20 mm 8 different colours
Cable lay up	8 coaxials twisted to the bundle
Sheath	PVC 25.3 mm ± 0.5 ivory, RAL 1001

S-2YCCYY 8 x 0.6/3.7D – 75 Ω PVC

Electrical properties

at 20°C

DC resistance	Inner conductor	≤ 65 Ω/km
Mutual capacitance		67 nF/km
Characteristic impedance	at 10 MHz	75 Ω ± 1.5 Ω
Velocity ratio		66 %
Transfer impedance	10 MHz	≤ 7.0 mΩ/m
Max. operating voltage		2 kV
Test voltage	Inner/Outer conductor	6.0 kV _{DC} 1 min
Insulation resistance		≥ 10 GΩ*km

Electrical data

at 20°C

Attenuation (dB/100m)		Crosstalk (dB/500m or 250m)		Return loss (dB)	
Frequency (MHz)		Frequency (MHz)		Frequency (MHz)	
1	≤ 1.1	0.3 – 2.3	≥ 75	10	≥ 40
2	≤ 1.6	2.3 – 10	≥ 85		
4	≤ 2.2	10 – 200	≥ 100		
10	≤ 3.5				
17	≤ 4.5				
50	≤ 7.7				
70	≤ 9.1				
100	≤ 10.9				
140	≤ 12.9				
200	≤ 15.8				

Technical data

Product code	Designation	Type	Outer diameter mm	Weight kg/km	Standard delivery length m	Drum size EW	Gross weight kg	Copper content	Tensile force N
1003339	S-2YCCYY	8 x 0.6/3.7D	25.3	755	250 ± 10	1000/500 /548	240	280	1920
CS270430 1	S-2YCCYY	8 x 0.6/3.7D	25.3	755	250 ± 10	1000/500 /548	240	280	1920
1008065	S-2YCCYY	8 x 0.6/3.7D	25.3	755	250 ± 10	1000/500 /548	240	280	1920

[PRODUCT CODE TABLE]

S-2YCCYY 8 x 0.6/3.7D – 75 Ω PVC

© PRYSMIAN GROUP 2008, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.