



Group

## HTC-50-1-1, 0.5Lz/1.5, CEH50

**Coaxial and Triaxial FRNC-High Voltage Low Power Cables acc. To CERN and DESY Specifications** 



## Application

see product overview

## **Standards**

acc. to Cern Spec. 477

## Flame resistance

acc. to IEC 60332-1

## Construction

Inner conductor	stranded copper wires, tinned, 7x 0.17, diameter 0.51 mm					
Semiconductive layer	semiconductive PE, diameter 0.70 mm					
Insulation	XPE crosslinked, diameter 1.50 mm					
Semiconductive layer	semiconductive PE, diameter 1.7 mm					
Outer conductor	copper braid, bare					
Wrapping	Mica tape					
Sheath	FRNC, flame retardant, non corrosive Copolymer, diameter 3.2 mm					
Colour	red RAL 3002					
Printing	DRAKA COMTEQ – manufacturing year					
CERN-Spec 477 Rev.1	HTC-50-1-1 meter marking and batch number					
Printing	DRAKA COMTEQ – manufacturing year					
CERN-Spec 477 Rev. 2	CEH50 meter marking and batch number					

LINKING THE FUTURE

www.prysmiangroup.com



at 20°C



# HTC-50-1-1, 0.5Lz/1.5, CEH50

## **Mechanical properties**

Minimum bending radius (during Installation)	without load	5 x D (D= outer diameter)		
	with load	10 x D (D= outer diameter)		
Temperature range		-25° C to + 70° C		
Radiation resistance		$\geq 10^{6} \text{ Gy} (= 10^{8} \text{ rad})$		
Fire propagation test		cables < 10 mm acc. to IEC 60332-1		
		cables > 10 mm acc. to IEC 60332-2-		
		24		
Corrosivity		acc. to IEC 60754-2		
Smoke density		acc. to IEC 61034		

#### **Electrical properties**

DC resistance	Inner conductor	≤ 120 Ω/km
	Outer conductor	≤ 42.8 Ω/km
Mutual capacitance		167 pF/m
Characteristic impedance	1 MHz	42 Ω
Operating voltage		5 kV <sub>DC</sub>
Test voltage	Inner/Outer conductor	12.5 kV <sub>DC</sub>
Insulation resistance		≥ 5 GΩ*km
Partial discharge test		5.3 kV <sub>rms</sub>
Discharge pulse magnitude		≤ 20 pC

All further requirements acc. to CERN Spec. 477 Rev. 2

#### **Technical data**

Product code	Desig- nation	Туре	Brand name	Outer dia- meter	Weight	Standard delivery length	Drum size	Gross weight	Copper content	Tensile force
				mm	kg/km	m	*PWD	kg		Ν
60013942	2xCH	0.5Lz/1.5	CEH50	3.2	16.2	1000	400/120/ 280	18.2	7.0	42

\*PWD (Plywood drum)

[PRODUCT CODE TABLE]

© PRYSMIAN GROUP 2013, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.

www.prysmiangroup.com