

S-02Y(St)CY 0.41/1.9AF – 75 Ω PVC

Coaxial SDH-Switch Board Cables acc. to Belgacom TR-SP. 130



Application

Standards

acc. to Belgacom specification TR-SP. 130

Flame resistance

Construction

Inner conductor	copper wire, tinned, diameter 0.41 mm ± 0.02 mm
Insulation	Foam-PE 1.9 mm ± 0.05
1. Outer conductor	Al-PET-Al-foil
2. Outer conductor	copper braid, tinned
Sheath	PVC 3.1 mm ± 0.01 mm black RAL 9001

S-02Y(St)CY 0.41/1.9AF – 75 Ω PVC

Electrical properties

at 20°C

DC resistance	Inner conductor	≤ 145 Ω/km
Mutual capacitance		60 nF/km
Characteristic impedance	at 1 MHz	75 Ω ± 3.0 Ω
Velocity ratio		78 %
Transfer impedance	30 MHz	≤ 10 mΩ/m
Max. operating voltage		0.750 kV
Test voltage	Inside/Outer conductor	1.5 kV _{rms} 1 min
Insulation resistance		≥ 10 GΩ*km

Electrical data

at 20°C

Attenuation (dB/100m)		Crosstalk (dB/500m or 250m)		Return loss (dB)	
Frequency (MHz)		Frequency (MHz)		Frequency (MHz)	
1	≤ 1.8	0.3 – 1	≥ 60	0.3 – 1	≥ 22
2	≤ 2.7	1 – 34	≥ 80	1 – 34	≥ 27
4	≤ 3.8				
10	≤ 5.9				
17	≤ 7.6				
20	≤ 8.3				
70	≤ 15.3				
100	≤ 18.5				
140	≤ 21.9				
200	≤ 26.2				

Technical data

Product code	Designation	Type	Outer diameter mm	Weight kg/km	Standard delivery length m	Drum size EW/ring	Gross weight kg	Copper content	Tensile force N
1003340	S-02Y(St)CY	0.41/1.9Dz AF	3.1	14	500 ± 20	300/150 /160	8.5	7.5	50

Product Code Table

Product Description	Product Code	PG Reference Code	PG Part Number
S-02Y(ST)CY 1X0.41/1.9 TR-SP.130		60013873	60013873

S-02Y(St)CY 0.41/1.9AF – 75 Ω PVC

© PRYSMIAN GROUP 2008, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.