

## HTC-50-5-1, 0.96Lz/4.7AF, CEH54

**Coaxial and Triaxial FRNC-High Voltage Low Power Cables acc. to CERN and DESY Specifications**



### Application

see product overview

### Standards

acc. to CERN-Specification 477 rev. 2

### Flame resistance

IEC 60332-1

### Construction

Inner conductor	stranded copper wires, tinned, 7x0.32, diameter 0.96 mm
Semiconductive layer	semiconductive PE, , diameter 1.70 mm
Insulation	XPE, crosslinked, , diameter 4.7 mm
Semiconductive layer	semiconductive PE, , diameter 5.1 mm
Outer conductor	copper braid, tinned
Wrapping	Al-PETP-Al-foil
Sheath	FRNC, flame retardant, non corrosive Copolymer, diameter 8.6 mm
Colour	red RAL 3002

### Mechanical properties

Minimum bending radius (during Installation)	without load	5 x D (D= outer diameter)
	with load	10 x D (D= outer diameter)
Temperature range		-25° C to + 70° C
Radiation resistance		≥ 10 <sup>6</sup> Gy (= 10 <sup>8</sup> rad)
Fire propagation test		cables < 10 mm acc. to IEC 60332-1
		cables > 10 mm acc. to IEC 60332-2-24
Corrosivity		acc. to IEC 60754-2
Smoke density		acc. to IEC 61034

## HTC-50-5-1, 0.96Lz/4.7AF, CEH54

### Electrical properties

at 20°C

DC resistance	Inner conductor	≤ 33 Ω/km
Mutual capacitance		120 pF/km
Characteristic impedance	at 1 MHz	54 Ω
Operating voltage		20 kV <sub>DC</sub>
Test voltage	conductor/screen	50 kV <sub>DC</sub>
Insulation resistance		5 GΩ*km
Partial discharge test		21.2 kV <sub>rms</sub>
Discharge pulse magnitude		≤ 20 pC

### Technical data

Product code	Designation	Type	Brand name	Outer diameter mm	Weight kg/km	Standard delivery length m	Drum size *OWD	Gross weight kg	Copper content	Tensile force N
1002776	2XC(St)H	0.96Lz/ 4.7 AF	HTC-50- 5-1 CEH54	8.6	95	1000	710/3 00/44 8	125	30.4	145

\*OWD (One way drum)

### Product Code Table

Product Description	Product Code	PG Reference Code	PG Part Number
CEH54 (HTC-50-5-1 0.96Lz/4.7AF)		60013933	<b>60013933</b>

© PRYSMIAN GROUP 2008, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.