


# S-09YS(St)CH 8 x 2 x 0.4/0.8 – 120 Ω

Symmetrical SDH-Switch Board Cables acc. to FTZ TS 0031/96



## Application

## Standards

acc. to FZT TS 0031/96

## Flame resistance

## Construction

Conductor	copper wire, bare, diameter 0.4 mm
Insulation	Foam-Skin-PP 0.8 mm
Core identification	1. quad: wt-bl, tq-vi 2. quad: wt-or, tq-vi 3. quad: wt-gn, tq-vi 4. quad: wt-br, tq-vi
Twisting	4 cores to the quad
Cable lay up	4 quads to the bundle
Wrapping	PET-foil
Overall screen	1 x PET-Al-foil + drain wire, tinned + copper braid, tinned
Sheath	FRNC-material ( Flame Retardant Non Corrosive ), 7.1 mm grey, RAL 7032
Printing	<b>DRAKA</b> S-09YS(St)CH 8x2x0.4 + batch no. + meter marking

## S-09YS(St)CH 8 x 2 x 0.4/0.8 – 120 Ω

### Electrical properties

at 20°C

Loop resistance		276.4 Ω/km ± 19.6 Ω/km
Mutual capacitance		≤ 45 nF/km
Capacitance unbalance	at 800 Hz	
	K <sub>1</sub>	0 ± 500 pF/km
	K <sub>9-12</sub>	0 ± 500 pF/km
	E <sub>12</sub>	0 ± 1500 pF/km
Characteristic impedance	at 1 MHz	120 Ω ± 12 Ω
Test voltage	core/core	1000 V <sub>DC</sub>
	core/screen	1000 V <sub>DC</sub>
Insulation resistance		≥ 10 GΩ*km

### Electrical data

at 20°C

Frequency (MHZ)	Attenuation (dB/km)	Near end crosstalk (within the quads) (dB/100m)	Far end crosstalk (within the quads) (dB/100m)	Screening factor (dB/km)	
				Frequency (MHz)	
1	26	≥ 50	≥ 60	30-900	≥ 80

### Technical data

Product code	Designation	Type	Outer diameter	Weight	Standard delivery length	Drum size	Gross weight	Copper content	Tensile force
			mm	kg/km	m	KTG/ring	kg		N
1007999	S-09YS(St)CH	8x2x0.4/0.8	7.1	65	1000	071	90	47	170

### Product Code Table

Product Description	Product Code	PG Reference Code	PG Part Number
S-09YS(ST)CH 8x2x0.4		60015088	<b>60015088</b>

© PRYSMIAN GROUP 2010, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.