



UC LR22 10Gbit S/FTP LSHF-FR B2_{ca} s1a d1 a1

S/FTP LONG REACH cable AWG22/1



Application

Primary (Campus), Secondary (Riser), Tertiary (Horizontal)
IEEE 802.3: 10Base-T, 100Base-T, 1000Base-T, 10GBase-T; IEEE 802.5
ISDN, TPDDI, ATM, CATV, IP Cameras, Broadband Video, SOHO-Cabling

120m range in the Channel E_A for 10Gbit transmissions guaranteed * / **

Standards

EN 50173-1; ISO/IEC 11801; EN 50288-9-1; IEC61156-5; IEC61156-7

Fire rating

EN 50399. Class B2_{ca} s1a d1 a1
LSHF-FR (LSOH-FR): IEC 60332-1; IEC 60332-3-24; IEC 60754-2; IEC 61034;

Construction

Conductor	Bare copper wire Ø 0.64 mm (AWG22)
Insulation	PE, Ø 1.6 mm
Twisting	2 cores to the pair
Cable lay up	4 pairs
Pair screen	Al-laminated plastic foil around each pair
Overall screen	Copper braid, tinned Ø 7,0mm
Sheath	Halogen free, fire retardant sheathing material; LSHF-FR, blue RAL 5024

Mechanical Properties

Bending radius	Installation	4 x D
	Installed	8 x D
Temperature range	During operation	-20°C to + 60°C
	During installation	0°C to + 50°C

* 105m Permanent Link PL2 garantiert

** Requires suitable components and patch cable

UC LR22 10Gbit S/FTP LSHF-FR B2_{ca} s1a d1 a1

Electrical Properties

at 20°C

DC loop resistance		≤ 110 Ω/km	
Resistance unbalance		≤ 2%	
Insulation resistance	(500 V)	≥ 5000 MΩxkm	
Capacitance	at 800 Hz	Nom. 43 nF/km	
Capacitance unbalance	(pair to ground)	≤ 1200 pF/km	
Mean Characteristic impedance	@ 100 MHz	100 ± 5 Ω	
Nominal velocity of propagation		79%	
Propagation delay		450 ns/100 m	
Delay skew		15 ns/100 m	
Transfer impedance	bei 1 MHz	≤ 5 mΩ /m	Grade 1
	bei 10 MHz	≤ 5 mΩ /m	
	bei 30 MHz	≤ 10 mΩ /m	
Coupling attenuation		≥ 85 dB	Type 1
Segregation classification acc. EN 50174-2			„d“

Nominal Transmission characteristics

acc. Cat.7 at 20°C

f (MHz)	Attenuation (dB/100m)	NEXT (dB)	PS-NEXT (dB)	ACR (dB/100m)	PS-ACR (dB/100m)	ELFEXT (dB/100m)	PS-ELFEXT (dB/100m)	Return loss (dB)
1,0	1,8	100	97	98	95	105	103	20
4,0	3,4	100	97	97	94	93	91	23
10,0	5,4	100	97	95	92	85	83	25
16,0	6,8	100	97	93	90	81	79	25
20,0	7,7	100	97	92	89	79	77	25
31,2	9,6	100	97	90	87	75	73	24
62,5	13,7	100	97	86	83	69	67	22
100,0	17,4	100	97	83	80	65	63	20
125,0	18,6	95	92	76	73	63	61	19
155,5	19,5	95	92	75	69	61	59	19
175,0	22,1	92	89	70	67	60	58	18
200,0	25,0	92	89	67	64	59	57	18
250,0	28,1	90	87	62	59	57	55	17
300,0	30,9	89	86	58	55	55	53	17
450,0	37,4	87	84	50	47	52	50	17
600,0	44,8	85	82	40	37	49	47	17
1000,0	58,4	82	79	24	21	45	43	17

UC LR22 10Gbit S/FTP LSHF-FR B2_{ca} s1a d1 a1

Product order data

Product reference code	Cable type	Brand name	Outer diameter	Euro Class	Fire load	Weight	Copper content	Tensile force
			mm		MJ/km	kg/km		N
60066017	J-02YSCH 4x2x0.64 PiMF	UC LR22 10Gbit S/FTP 4P LSHF-FR B2 _{ca}	8.5	B2 _{ca} s1a d1a1	545	75	43	340

© PRYSMIAN GROUP 2014, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.