


Prysmian Group

A brand of the

JAMAK[®] -HF

Symmetrical Data Cable for industrial Control Equipment



Application

These symmetrical data transmission cables are used in control and supervision center for industrial sites. They are suitable for fixed installation inside housings.

Flame resistance

Oxygen Index LOI acc. to ASTM-D-2863 Smoke emmison acc. to ASTM-D-2843 IEC 60332-3C > 30 % 10 - 20 %

Construction

Conductor	Tinned stranded copper 7x 0.29 mm		
Insulation	PE (2Y)		
Conductor identification	a-conductor blue; b-conductor red		
Stranding	2 conductors to pair		
Stranding to core	(0+4)		
Pair shielding	Laminated AL-foil + copper drain wire 0.5 mm ²		
Overall shielding	Laminated AL-foil + copper drain wire 0.5 mm ²		
Outer sheath	LSZH (H), grey		

LINKING THE FUTURE

www.prysmiangroup.com



JAMAK[®] -HF

Mechanical properties

Operating temperature	- 30 °C to + 70 °C		
Min. Installation temperature	- 5 °C		

Electrical properties	at 20°C			
Loop resistance	81 Ω/km			
Insulation resistance (at 500 V, 1 min.)	2 GΩ*km			
Capacitance at 800 Hz	85 nF/km			
Max. operating voltage	75 V			
Relative velocity factor NVP	0.66			
Impedance (at 10 MHz)	70 Ω +/- 10 %			
Frequency	attenuation			
[kHz]	[dB/100 m]			
9.6	0.3			
19.2	0.5			
64	0.7			
100	0.9			
200	1.6			
1000	4.5			

Technical data

Part no.	Туре	Dimension	Outer diameter mm	Standard length m	weight kg/km	Copper content
Not yet defined	JAMAK-HF	2x(2+1)x0.5	8.0±0.5	1000	70	35
Not yet defined	-	4x(2+1)x0.5	9.5±0.5	1000	110	65
Not yet defined		8x(2+1)x0.5	13.0±0.5	1000	200	125
Not yet defined		12x(2+1)x0.5	15.0±0.8	1000	280	185
Not yet defined		24x(2+1)x0.5	21.0±1.0	1000	530	365
Not yet defined	-	48x(2+1)x0.5	29.0±1.5	500	1000	725

[PRODUCT CODE TABLE]

A brand of the



LINKING THE FUTURE

www.prysmiangroup.com





Prysmian Group

A brand of the

© PRYSMIAN GROUP 2012, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian Group: any modification or alteration afterwards of product may give different result.

The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian Group. The information is believed to be correct at the time of issue. Prysmian Group reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorised by Prysmian Group.

www.prysmiangroup.com