

## BendBright™ XS Single-Mode Fibre

ITU-T G.657.A2



Issue date: November 2023  
Supersedes: August 2010

### Applicable Standards

- IEC/EN 60793-2-50 type B-657.A2
- IEC/EN 60793-2-50 type B-652.D
- ITU-T Recommendation G.657.A2
- ITU-T Recommendation G.652.D

### Optical Specifications

#### Attenuation

Attribute	Units	1310 nm	1383 nm <sup>1</sup>	1460 nm	1550 nm	1625 nm
Attenuation	dB/km	≤ 0.35	≤ 0.35	≤ 0.25	≤ 0.20	≤ 0.21

<sup>1</sup> Including H2-aging according to IEC 60793-2-50, type B.1.3

#### Attenuation vs. Wavelength

Wavelength Range (nm)	Reference λ (nm)	(dB/km)
1285 – 1330	1310	≤ 0.03
1525 - 1575	1550	≤ 0.02
1460 - 1625	1550	≤ 0.04

#### Point discontinuities

No point discontinuity greater than 0.05 dB at 1310 nm and 1550 nm.

#### Attenuation variation vs. Bending

Number of Turns	Wavelength (nm)	Induced Attenuation (dB)
10 turns on a R = 15 mm mandrel	1550	≤ 0.03
10 turns on a R = 15 mm mandrel	1625	≤ 0.1
1 turn on a R = 10 mm mandrel	1550	≤ 0.1
1 turn on a R = 10 mm mandrel	1625	≤ 0.2
1 turn on a R = 7.5 mm mandrel	1550	≤ 0.5
1 turn on a R = 7.5 mm mandrel	1625	≤ 1.0

## Mode Field Diameter

Wavelength (nm)	Units	MFD
1310	μm	8.8 ± 0.4
1550	μm	9.8 ± 0.5

## Cutoff Wavelength

Cable Cutoff Wavelength ( $\lambda_{cct}$ )	≤ 1260 nm
---	-----------

## Chromatic Dispersion

Wavelength (nm)	Units	Chromatic Dispersion
In the interval 1285 – 1330	ps/[nm.km]	≤  3.7
At 1550	ps/[nm.km]	≤ 18.5
At 1625	ps/[nm.km]	≤ 23.0
Zero Dispersion Wavelength, $\lambda_0$	nm	1300 - 1324
Slope ( $S_0$ ) at $\lambda_0$	ps/(nm <sup>2</sup> · km)	≤ 0.092

## Polarization Mode Dispersion (PMD)

Attribute	Units	Specified Values
PMD Link Design Value <sup>2</sup>	ps/√km	≤ 0.06
Max. individual Fiber	ps/√km	≤ 0.1

<sup>2</sup> According to IEC 60794 –3, Ed 3 (Q=0.01%)

## Typical Values

Attribute	Units	1310 nm	1550 nm	1625 nm
Effective group index	-	1.467	1.468	1.468
Rayleigh Backscatter Coefficient for 1 ns pulse width	dB	- 79.1	- 81.4	- 82.2

## Geometrical Specifications

### Glass Geometry

Attribute	Units	Specified Values
Cladding Diameter	μm	125.0 ± 0.7
Core - Cladding Concentricity Error	μm	≤ 0.5
Cladding non-Circularity	%	≤ 0.7
Fiber Curl (radius)	m	≥ 4

### Coating Geometry

Attribute	Units	Specified Values
Coating Diameter	μm	242 ± 7
Coating - Cladding Concentricity Error	μm	≤ 12
Coating non-Circularity	%	≤ 5

## Mechanical Specifications

### Proof Test <sup>3</sup>

The entire spool length is subjected to a tensile proof stress  $\geq 0.7$  GPa (100 kpsi) ; 1% strain equivalent

<sup>3</sup> Higher proof test available upon request

### Coating Performance

Attribute	Units	Specified Values
Average Coating Strip Force, unaged and aged <sup>4</sup>	N	$1 \leq F_{\text{avg-strip}} \leq 3$
Peak Coating Strip Force, unaged and aged <sup>4</sup>	N	$1.2 \leq F_{\text{peak-strip}} \leq 8.9$

<sup>4</sup> Aging at 23°C, 30 days

### Fibre Strength

Attribute	Units	Specified Values
Dynamic Tensile Strength (0.5 meter gauge length), unaged and aged <sup>5</sup>	GPa	median > 3.8 (550 kpsi)
Dynamic Fatigue, unaged and aged <sup>5</sup>	-	$n_d \geq 20$

<sup>5</sup> Aging at 85°C, 85% RH, 30 days

### Environmental Specifications

Environmental test	Test Conditions	Induced attenuation at 1550, 1625 nm (dB/km)
Temperature Cycling	- 60°C to 85°C	$\leq 0.05$
Temperature - Humidity Cycling	- 10°C to 85°C, 4-98% RH	$\leq 0.05$
Water Immersion	14 days; 23°C	$\leq 0.05$
Dry Heat	30 days; 85°C	$\leq 0.05$
Damp Heat	30 days; 85°C; 85% RH	$\leq 0.05$

### Others

Length	Up to 50.4 km per spool
Coating	Acrylate coating; ColorLock™ XS and Clear

All measurements in accordance with ITU-T G650 recommendations