

BendBright™ OM3 – BiDi Fiber

OM3-BiDi optimized for Advanced 800G and Terabit BiDi applications



APPLICABLE STANDARDS

- IEC / EN 60793-2-10: type A1-OM3
- ISO / IEC 11801: Category OM3
- TIA / EIA 492 AAAF

Issue Date: February 2025

Supersedes:

OPTICAL SPECIFICATIONS

BANDWIDTH (EMB)

Attribute	Units	Specified Values
Effective Modal Bandwidth at 850 nm	MHz·km	≥ 2890
Effective Modal Bandwidth at 910 nm	MHz·km	≥ 2220

BANDWIDTH (OFL)

Attribute	Units	Specified Values
Overfilled Modal Bandwidth at 850 nm	MHz·km	≥ 1500
Overfilled Modal Bandwidth at 1300 nm	MHz·km	≥ 500

ATTENUATION

Attribute	Units	Specified Values
Attenuation coefficient at 850 nm	dB/km	≤ 2.3
Attenuation coefficient at 910 nm	dB/km	≤ 1.8
Attenuation coefficient at 1300 nm	dB/km	≤ 0.6

NUMERICAL APERTURE

Attribute	Specified Values
Numerical aperture	0.200 ± 0.015

MACROBENDING LOSS

Conditions	Wavelength	Units	Specified Values
Mandrel Radius = 7.5 mm, 2 Turns	850 / 1300 nm	dB	≤ 0.2 / ≤ 0.5
Mandrel Radius = 15 mm, 2 Turns	850 / 1300 nm	dB	≤ 0.1 / ≤ 0.3

MULTIMODE SYSTEM REACH

IEEE Standard or MSA	Units	Transmission Distance
Terabit BiDi 1.6T-SR8.2	m	45
Terabit BiDi 1.6T-VR8.2	m	30
Terabit BiDi 800G-SR4.2	m	45
Terabit BiDi 800G-VR4.2	m	30
800GBASE-SR8	m	60
800GBASE-VR8	m	30
400GBASE-SR4.2	m	70
400GBASE-SR8	m	70

CHROMATIC DISPERSION

Attribute	Conditions	Units	Specified Values
Zero Dispersion Wavelength, λ_0		nm	$1295 \leq \lambda_0 \leq 1340$
Zero Dispersion Slope, S_0	$1295 \leq \lambda_0 \leq 1310$	ps/[nm ² ·km]	≤ 0.105
	$1310 \leq \lambda_0 \leq 1340$	ps/[nm ² ·km]	$\leq 0.000375 (1590 - \lambda_0)$

BACKSCATTER CHARACTERISTICS ¹

Attribute	Conditions	Units	Specified Values
Point Discontinuity ²	850 nm, 1300 nm	dB	≤ 0.1
Irregularities over fibre length	850 nm, 1300 nm	dB	≤ 0.1
Group Index of Refraction at 850 nm	-	-	1.482 (typical)
Group Index of Refraction at 1300 nm	-	-	1.477 (typical)

¹ OTDR measurement with 0.5 μ s pulse width.

² Mean of bi-directional measurement

GEOMETRICAL SPECIFICATIONS

GLASS GEOMETRY

Attribute	Units	Specified Values
Core Diameter	μ m	50 ± 2.5
Core non-Circularity	%	≤ 5
Core-Cladding Concentricity Error	μ m	≤ 1.0
Cladding Diameter	μ m	125.0 ± 1.0
Cladding non-Circularity	%	≤ 0.7

COATING GEOMETRY

Attribute	Units	Specified Values
Coating Diameter	μm	242 ± 7
Coating non-Circularity	%	≤ 5
Coating-Cladding Concentricity Error	μm	≤ 10

MECHANICAL SPECIFICATIONS

Proof Test ³

The entire spool length is subjected to a tensile proof stress ≥ 0.7 GPa (100 kpsi) ; 1% strain equivalent

³ Higher proof test available upon request

COATING PERFORMANCE

Attribute	Units	Specified Values
Average Coating Strip Force, unaged and aged ⁴	N	1 ≤ F _{avg-strip} ≤ 3.0
Peak Coating Strip Force, unaged and aged ⁴	N	1.3 ≤ F _{peak-strip} ≤ 8.9

⁴ Aging at 23°C, 30 days

FIBRE STRENGTH

Attribute	Units	Specified Values
Dynamic Tensile Strength (0.5 meter gauge length), unaged and aged ⁵	GPa	median > 3.8 (550 kpsi)
Dynamic Fatigue, unaged and aged ⁵	-	n _d ≥ 20

⁵ Aging at 85°C, 85% RH, 30 days

ENVIRONMENTAL SPECIFICATIONS

Environmental test	Test Conditions	Induced attenuation at 850, 1300 nm (dB/km)
Temperature Cycling	-60°C to +85°C	≤ 0.1
Temperature - Humidity Cycling	-10°C to +85°C, 4-98% RH	≤ 0.1
Water Immersion	30 days; 23°C	≤ 0.1
Dry Heat	30 days ; 85°C	≤ 0.1
Damp Heat	30 days; 85°C; 85% RH	≤ 0.1

OTHERS

Attribute	Specified Values
Length	8.8 km per spool
Coating	Acrylate Coating (Clear)

All measurements in accordance with ITU-T G650 recommendations

© PRYSMIAN GROUP 2024, All Rights Reserved

All sizes and values without tolerances are reference values. Specifications are for product as supplied by Prysmian: any modification or alteration afterwards of product may give different result. The information contained within this document must not be copied, reprinted or reproduced in any form, either wholly or in part, without the written consent of Prysmian. The information is believed to be correct at the time of issue. Prysmian reserves the right to amend this specification without prior notice. This specification is not contractually valid unless specifically authorized by Prysmian.